



## Versamate Series 200A 3 Pole 4 Wire Receptacle Assembly

By Killark  
Catalog # [VR20422](#)



200A 3 Pole 4 Wire Receptacle Assembly.

### General

EU RoHS Indicator	Contact Manufacturer
Finish Type	Finition époxy/polyester en poudre cuite
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
Type	
UPC	783936833149

### Dimensions

Dimensions	7.87 in x 6.83 in x 7.59 in
Height	7.59 in
Length	7.87 in
Width	6.83 in

### Electrical Ratings

Amperage Rating	200 A
Frequency Rating	50-400 Hz
Voltage Rating	<ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul>

### Conductor Related

Number Of Wires	3
-----------------	---

### Product Assets

[Certifications - Versamate Series UL Certification](#)  
[Certifications - CSA Certificate - 200 Amp Versamate Series](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Versamate 200 Amp IOM K1206](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-VR20422-SPEC-EN | REV 5/2024