



Plastic Box, 18 Cubic Inches, Single Gang With Flush Bracket

By Raco
Catalog # 2001R

1-Gang Plastic Box 18 in³, Flush Bracket, ½" Setback, 4-cable Clamp, High-Strength Plastic Resin (50-Pack).



Features

- For use with non-metallic sheathed cable
- Angled screw holder holds and directs wood screws at a convenient angle to the stud making installation faster and easier
- Ruler markings ensure accurate and consistent box placement at various depths reducing installation time
- Drill points makes drilling for low voltage cables quick, easy and accurate
- Offset mounting wings provide stable mounting of the box including double-drywall installations

Application

Accommodates wiring devices such as switches and receptacles

General

Bracket Setback	0.50
Color	<ul style="list-style-type: none">• Yellow• Jaune
Fire Resistance	Yes
Material	Thermoplastic Resin
Number of Gang(s)	1-Gang
Type	<ul style="list-style-type: none">• Non-Metallic Box• Non-Metallic Box
UPC	805035000038
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2.81 in
Cubic Capacity	50.2425 cu.in
Depth	2.75 in
Height	6.3 in
Weight	0.208 lb
Width	2.9 in

Certifications and Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	50
Pallet Quantity	1800

Product Assets

[3D Product View](#)
[Brochures - H3672 Banana Boxes](#)

Related Products

[2709 - 2-9/16 in. Cable Protector](#)



A proud member of the Hubbell Family.