



Net Select, Module, 6-Way Coax, 2.3GHz, Plastic

By Hubbell Premise Wiring
Catalog Number [NSOVM62G](#)



Net Select, Module, 6-Way Coax, 2.3GHz, Plastic.

Application

CATV

General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	6-Way Coax, 2.3GHz
Material - Mounting Hardware	Screw Mounting
Style	Coaxial Splitter
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Coaxial Splitter
UPC	883778504396

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• RoHS Compliant• UL and cUL Listed
----------------------	--

Product Assets

[Catalog Page - Premise Catalog Page V-8](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-NSOVM62G-SPEC-EN | REV 5/2023