



Hubbell Premise Wiring

Net Select, Module, 8-Way Coax, 1GHz, Plastic

By Hubbell Premise Wiring
Catalog Number [NSOVM8](#)



Net Select, Module, 8-Way Coax, 1GHz, Plastic.

Application

CATV

General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	8-Way Coax, 1GHz
Material - Mounting Hardware	Screw Mounting
Style	Coaxial Splitter
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Coaxial Splitter
UPC	883778504402

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • RoHS Compliant • UL and cUL Listed
----------------------	---

Product Assets

[Catalog Page - Premise Catalog Page V-8](#)



A proud member of the Hubbell Family.