
CO2 Series

200 A 120/240 V; combination with or without breaker

Product specifications

- Conductor range (line and load): 6 AWG-250KCMIL
- Aluminum tunnel type connectors for both load and line sides
- · For overhead and underground services
- With factory-installed neutral conductor
- Bottom compartment has provision for 2 pole circuit breaker (max 200 A) 10 kA breakers (22 kA breaker where indicated HI)
- Suitable for 120/240 V single-phase service entrance for mobile homes, trailers, temporary services, recreational parks and other commercial and residential locations
- Factory installed adjustable bracket for field installation of Siemens type QJ,QJH,QR,QRH and SQD TYPE QB and Eaton type ED
- Factory installed 2 pole circuit breaker, 10,000 arms interrupting capacity UP TO 22 kA Siemens or ABB breaker
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces




			P	Dimensions (in.) Weight each				
	C = k = = =							
	Cat. no. 4 Jaw	Туре	Description	н	W	D	lb	kg
CO2-200	CO2	Overhead	Provision for 1 X 2 pole 10 kA rated circuit breaker	323/4	1113/16	57⁄16	28	12.7
	CO2-100G	Underground	Comes complete with ABB type A2A 2 pole 100 A 10 kA rated circuit breaker	32¾	1113/16	5 ½ 16	30	13.6
	CO2-125	Overhead	Comes complete with ABB type A2A 2 pole 125 A 10 kA rated circuit breaker	32¾	11 ¹³ ⁄16	57/16	30	13.6
	CO2-125G	Underground	Comes complete with ABB type A2A 2 pole 125 A 10 kA rated circuit breaker	32¾	11 ¹³ /16	57⁄16	30	13.6
	CO2-125-5V	Overhead	Comes complete with ABB type A2A 2 pole 125 A 10 kA rated circuit breaker, complete with 5th jaw	32¾	1113/16	5 ½ 16	30	13.6
	CO2-125HI	Overhead	Comes complete with ABB type A2N 2 pole 125 A 22 kA rated circuit breaker	32¾	11 ¹³ / ₁₆	5 7⁄16	30	13.6
	CO2-150	Overhead	Comes complete with ABB type A2A 2 pole 150 A 10 kA rated circuit breaker	32¾	11 ¹³ /16	57/16	30	13.6
	CO2-150G	Underground	Comes complete with ABB type A2A 2 pole 150 A 10 kA rated circuit breaker	32¾	11 ¹³ / ₁₆	57⁄16	30	13.6
	CO2-150-5V	Overhead	Comes complete with ABB type A2A 2 pole 150 A 10 kA rated circuit breaker, complete with 5th jaw	32¾	1113/16	5 ½ 16	30	13.6
	CO2-150HI	Overhead	Comes complete with ABB type A2N 2 pole 150 A 22 kA rated circuit breaker	32¾	11 ¹³ / ₁₆	5 7⁄16	30	13.6
	CO2-200	Overhead	Comes complete with ABB type A2A 2 pole 200 A 10 kA rated circuit breaker	32¾	11 ¹³ /16	57⁄16	30	13.6
	CO2-200-5V	Overhead	Comes complete with ABB type A2A 2 pole 200 A 10 kA rated circuit breaker, complete with 5th jaw	32¾	1113/16	5 7⁄16	30	13.6
	CO2-200HI	Overhead	Comes complete with ABB type A2N 2 pole 200 A 22 kA rated circuit breaker	323/4	11 ¹³ / ₁₆	5 7⁄16	30	13.6
	CO2-200HI-G	Underground	Comes complete with ABB type A2N 2 pole 200 A 22 kA rated circuit breaker, complete with gutter	32¾	1113/16	5 7 / ₁₆	30	13.6
	CO2-200G	Underground	Comes complete with ABB type A2A 2 pole 200 A 10 kA rated circuit breaker, complete with gutter	323/4	1113/16	57/16	32.6	14.6
	CO2-G	Underground	Provision for 2 pole 200 A 10 kA rated circuit breaker, complete with gutterr	323/4	1113/16	5 ½ 16	28	12.7
	CO2-200GBC	Underground	Comes complete with ABB type A2A 2 pole 200 A 10 kA rated circuit breaker, complete with gutter & 3 in KOs.	32¾	1113/16	5 ½ 16	28	12.7

CO2 Series

200 A 120/240 V; combination with or without breaker

Diagrams




CO2M Series

200 A - Single-phase 120/240 V; combination with or without breaker and splitter

Product specifications

- Conductor range CO2M, CO2MS,CO2MS-2446, CO2MSU (line and load): 6 AWG-250 kcmil
- Conductor range CO2MSB-200, (line side and load neutral): 6 AWG-250 kcmil, (load side and neutral load): 6 AWG-300 kcmil
- For combination verhead/underground service only
- Cutler Hammer (Eaton) breaker to be field-installed
- With CO2FB braid connector (also available for field installation, cat. no. CO2FB-KIT) supplied with Siemens or ABB breaker
- Primarily used in: Alberta




		Туре		Dimer	nsions	Weight each		
	Cat. no.		Description	н	W	D	lb	kg
CO2MS	4 Jaw							
	CO2MS	Combination overhead/underground	Provision for field-installed Cutler Hammer (ED) 200 A 2 pole 10 kA rated circuit breaker, provision for pole mounting (splitter included)	39 %	12	5 7/16	42	19
	CO2MS-2446	Combination overhead/ underground	Provision for field-installed Cutler Hammer (ED) 200 A 2 pole 10 kA rated circuit breaker, provision for pole mounting, comes with 2446 connector (splitter included), Fortis Alberta approved	39 %	12	57/16	44	19.5
	CO2MSB-200	Combination overhead/underground	Comes complete with ABB type A2A 2 pole 200 A 10 kA rated circuit breaker, comes with neutral bar (splitter included)	403/s	12	5 7/16	47	21.3
	CO2MSU	Underground	Provision for field-installed Cutler Hammer (ED) 200 A 2 pole 10 kA rated circuit breaker, pedestal type for padmount applications (splitter included)	605/32	117/8	5 ²⁷ / ₆₄	59	26.8

CO2M Series

200 A – Single-phase 120/240 V; combination with or without breaker and splitter



Cat. no. CO2FB-KIT



 $\label{local_problem} \mbox{Diagram as reference only. Please contact your regional inside sales representative for other catalogue numbers and drawings pertaining to this series.}$