

# Eaton 5262B

Catalog Number: 5262B

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 15A, Industrial, Flush, 125V, Back and side, Brown, Brass, High-impact nylon face, 5-15R, Duplex, Screw, Glass-filled nylon



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	5262B
	<b>UPC</b>
	032664704277
<b>Product Length/Depth</b>	<b>Product Height</b>
1.32 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
0.88 in	0.001 lb
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL
NAFTA	NOM
	Federal Specification Classification 6233 01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

### Application

Industrial

### Device grade

Heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

Glass-filled nylon

### Color

Brown

### Connection type

Screw

### Allowable wire size

#14-10 AWG

## Resources

### Brochures

[Spec grade receptacles brochure](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 5262B](#)

[Arrow Hart heavy-duty straight blade duplex receptacles](#)

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)