

Eaton AH7810GD-C

Catalog Number: AH7810GD-C

Eaton manual motor controller, Canadian version, #14-10 AWG, 30A, Industrial, Wall, 600V, Front wired screw and clamp, Maintained contact, Gray, NEMA 1, Enclosure: SS, Three-pole, Single-gang, Three-phase, Toggle, Single-throw, Nylon

General specifications



Product Name

Eaton manual motor controller

Catalog Number

AH7810GD-C

UPC

040893658988

Product Length/Depth

6.3 in

Product Height

5.7 in

Product Width

6.4 in

Product Weight

1.58 lb

Compliances

RoHS Compliant
NAFTA

Certifications

cULus Listed

defaultTaxonomyAttributeLabel

Enclosure

NEMA 1

Special features

Canadian version

Type

Manual motor controller

Amperage Rating

30A

Voltage rating

600 V

Number Of Poles

Three-pole

Phase

Three-phase

Enclosure material

Stainless steel

Application

Industrial

Device grade

Industrial

Wiring method

Front wired screw and clamp

Contact type

Maintained

NEMA Rating

1

Switch type

Toggle switch

Mounting method

Wall

Closure type

Maintained

Number of gangs

1

Resources

Brochures

[Arrow Hart motor controllers and disconnects brochure](#)

Specifications and datasheets

[Eaton Specification Sheet - AH7810GD-C](#)

Number of positions

2

Allowable wire size

#14-10 AWG

Operating temperature

-20 to 65 °C

Material

Glass-filled nylon

Termination style

Front screw and clamp

Throw

Single-throw

Terminals

Copper-alloy, brass screw

Color

Gray



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia