

Eaton 5261W

Catalog Number: 5261W

Eaton Arrow Hart extra heavy-duty industrial specification grade single receptacle, #14-10 AWG, 15A, Industrial, Flush, 125V, Back and side, White, Brass, High-impact nylon face, 5-15R, Single, Screw, Glass-filled nylon, Core pack



General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty industrial specification grade single receptacle	5261W
	UPC
	032664400407
Product Length/Depth	Product Height
1.32 in	4.19 in
Product Width	Product Weight
0.88 in	0.21 lb

Certifications

UL
NOM
Federal Specification Classification 6233
01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Single receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Auto-grounding

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Glass-filled nylon

Packaging type

Core pack

Color

White

Connection type

Screw

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 5261W](#)

[Arrow Hart extra heavy-duty industrial grade straight blade receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

High-impact nylon face

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)