

Eaton IG8362W

Catalog Number: IG8362W

Eaton Arrow Hart extra heavy-duty hospital grade decorator duplex receptacle, #14-10 AWG, 20A, Healthcare, Flush, 125V, Back and side, White, Brass, High-impact nylon face, Glass-filled nylon base, 5-20R, Duplex, Screw, Glass-filled nylon, Core pack



General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty hospital grade decorator duplex receptacle	IG8362W
	UPC
	040893683409
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.92 in	0.37 lb

Certifications

UL
NOM
Federal Specification Classification 6233
01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Decorator duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Isolated ground

Auto-grounding

Terminal guards

Application

Healthcare

Device grade

Extra heavy-duty hospital grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Material

Glass-filled nylon

Packaging type

Core pack

Color

White

Connection type

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Arrow Hart extra heavy-duty hospital grade isolated ground straight blade receptacles](#)

[Eaton Specification Sheet - IG8362W](#)

Technical data sheets

[Arrow Hart extra heavy-duty hospital grade isolated ground straight blade decorator receptacles](#)

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Glass-filled nylon base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)