

# Eaton AH5662B

Catalog Number: AH5662B

Eaton Arrow Hart extra heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 15A, Industrial, Flush, 250V, Back and side, Brown, Brass, Glass filled Nylon, 6-15R, Duplex, Screw, Nylon, Core pack



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart extra heavy-duty industrial specification grade duplex receptacle	AH5662B
	<b>UPC</b>
	032664704215
<b>Product Length/Depth</b>	<b>Product Height</b>
1.32 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
1.36 in	0.17 lb

## Certifications

UL  
NOM  
Federal Specification Classification 6233  
01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

15A

### Voltage rating

250V

### Contact material

Brass

### Features

Terminal guards

Auto-grounding

### Application

Industrial

### Device grade

Extra heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

Nylon

### Packaging type

Core pack

### Color

Brown

### Connection type

Screw

## Resources

### Brochures

[Spec grade receptacles brochure](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - AH5662B](#)

[Arrow Hart extra heavy-duty industrial grade straight blade receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

6-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Glass filled nylon

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)