

Eaton 5469

Catalog Number: 5469

Eaton Arrow Hart ultra grip straight blade connector, #16-12 AWG, 20A, Industrial, 250V, Back wire, Black and white, Brass, Nylon, 6-20R, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Polycarbonate, Core pack

General specifications



Product Name	Catalog Number
Eaton Arrow Hart ultra grip straight blade connector	5469
	UPC
	032664390708

Product Length/Depth	Product Height
6.5 in	1.5 in

Product Width	Product Weight
3.5 in	0.175 lb

Certifications

UL

NOM

Federal Specification Classification 6221

02

Electrical Ratings

Amperage Rating

20A

NEMA configuration

6-20R

Voltage rating

250V

Wiring method

Back wire

Material Specifications

Color

White

Black

Contact material

Brass

Face/body material

Nylon

Material

Polycarbonate

Packaging type

Core pack

Product Specifications

Allowable wire size

#16-12 AWG

Application

Industrial

Connection type

Screw

Cord range

0.33-0.66" in diameter

Design type

Straight blade

Device grade

Extra heavy-duty industrial specification grade

Device type

Connector

Number Of Poles

Two-pole

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Style type

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 5469](#)

Straight body

Type

Connector



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)