

Eaton AHCL2130R

Catalog Number: AHCL2130R

Eaton Arrow Hart Color Coded Locking Receptacle, #14-8 AWG, 30A, Industrial, 3ØY 120/208 V, Blue, Black, Ultra grip, Glass filled Nylon, L21-30, Four-pole, Five-wire, Glass-filled Nylon, -40°C (w/o impact) to 70°C (-40°F to 158°F)



General specifications

Product Name	Catalog Number
Eaton Arrow Hart Color Coded Locking Receptacle	AHCL2130R
	UPC
	032664758454
Product Length/Depth	Product Height
1.62 in	3.64 in
Product Width	Product Weight
1.06 in	0.33 lb
Compliances	Certifications
RoHS Compliant	CSA Certified
NAFTA	UL Listed
	NOM
	Federal Specification Classification 6233 01

defaultTaxonomyAttributeLabel

Special features

Voltage Color Coding

Type

Locking Receptacle

Amperage Rating

30A

Voltage rating

3ØY 120/208 V

Application

Industrial

Wiring method

Back and side

Number of wires

5

Number Of Poles

Four-pole

Color

Black

Blue

Material

Glass filled nylon

Operating temperature

-40 to 70 °C (-40 to 158 °F)

Allowable wire size

#14-8 AWG

NEMA configuration

L21-30

Torque rating

20 lbf-inch

Design type

Ultra grip

Face/body material

Glass filled nylon

Resources

Multimedia

[Eaton Arrow Hart color coded locking devices](#)

Specifications and datasheets

[Arrow Hart color coded industrial grade L21-30 locking devices spec sheet](#)

[Eaton Specification Sheet - AHCL2130R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia