

# Eaton 4867AN-SP

Catalog Number: 4867AN-SP

Eaton Arrow Hart straight blade angled plug , #18-12 AWG, 15A, Commercial, 125V, Back wire, Yellow, Brass, Vinyl, 5-15P, Two-pole, three-wire, grounding, Screw, 0.25-0.66", Vinyl, Retail Box

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart straight blade angled plug	4867AN-SP
	<b>UPC</b>
	032664752261
<b>Product Length/Depth</b>	<b>Product Height</b>
1.63 in	5.5 in
<b>Product Width</b>	<b>Product Weight</b>
4.25 in	0.098 lb
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL
	NOM
	Federal Specification Classification 622102

## defaultTaxonomyAttributeLabel

### Device type

Plug

### Type

Angled plug

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Application

Commercial

### Device grade

Commercial specification grade

### Wiring method

Back wire

### Number of wires

3

### Number Of Poles

Two-pole

### Style type

Angled body

### Cord range

0.25-0.66" in diameter

### Material

Vinyl

### Packaging type

Retail Box

### Color

Yellow

### Connection type

Screw

### Allowable wire size

#18-12 AWG

### NEMA configuration

## Resources

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Multimedia

[Commercial and residential straight blade vinyl receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 4867AN-SP](#)

5-15P

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Vinyl

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)