

Eaton 2887

Catalog Number: 2887

Eaton straight blade connector , #18-12 AWG, 15A, Commercial, 125V, Back wire, Yellow, Brass, Armored vinyl, 5-15R, Two-pole, three-wire, grounding, Screw, Vinyl, Core pack



General specifications

Product Name	Catalog Number
Eaton straight blade connector	2887
UPC	Product Length/Depth
032664752292	2.75 in
Product Height	Product Width
7.5 in	3.25 in
Product Weight	Certifications
0.16 lb	cULus Listed
	NOM
	Federal Specification Classification 6221 02

defaultTaxonomyAttributeLabel

Device type

Connector

Special features

Armored

Type

Armored connector

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Armored

Application

Commercial

Device grade

Commercial specification grade

Wiring method

Back wire

Number of wires

3

Number Of Poles

Two-pole

Style type

Straight body

Material

Vinyl

Packaging type

Core pack

Color

Yellow

Connection type

Screw

Allowable wire size

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Commercial and residential straight blade vinyl receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 2887](#)

#18-12 AWG

NEMA configuration

5-15R

Design type

Straight blade

Face/body material

Armored vinyl

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)