

Eaton 2867-BOX

Catalog Number: 2867-BOX

Eaton straight blade plug , #18-12 AWG, 15A, Commercial, 125V, Back wire, Yellow, Brass, Armored vinyl, 5-15P, Two-pole, three-wire, grounding, Screw, 0.25-0.63", Vinyl, ED Box

General specifications



Product Name
Eaton straight blade plug

Catalog Number
2867-BOX

Product Length/Depth
1.519 in

Product Height
2.524 in

Product Width
1.519 in

Product Weight
0.115 lb

Compliances
RoHS Compliant

Certifications
cULus Listed
NOM

Photo is representative

Electrical Ratings

Amperage Rating

15A

Torque rating

15 lbf-inch

Voltage rating

125V

Wiring method

Back wire

Material Specifications

Color

Yellow

Contact material

Brass

Face/body material

Armored vinyl

Material

Vinyl

Packaging type

ED Box

Product Specifications

Allowable wire size

#18-12 AWG

Application

Commercial

Connection type

Screw

Cord range

0.25-0.63"

Design type

Straight blade

Device grade

Commercial specification grade

Device type

Plug

Features

Armored

Number Of Poles

Two-pole

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Resources

Style type

Straight body

Type

Armored plug



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)