

SCREWDRIVERS & NUTDRIVERS

MULTI-BIT SCREWDRIVERS

- MOST VERSATILE MULTI-BIT DRIVER
- EASY ACCESS BITS: IN-HANDLE BIT STORAGE
- DURABLE, ALL-METAL RATCHET: HIGHER TORQUE AND FASTER DRIVING
- REMOVABLE BIT HOLDER: POWER-TOOL READY WITH 1/4" HEX SHANK
- ERGONOMIC HANDLE WITH DURABLE OVERMOLD



NEW

PART #	DESCRIPTION	BIT TYPES
48-22-2900	14-in-1 Multi-Bit Screwdriver	P1, P2, SL 1/4", SL 3/16", SQ1, SQ2, SQ3, ECX1, ECX2, T10, T15, T20, T25 and 1/4" Nut Driver
48-22-2903	14-in-1 Ratcheting Multi-Bit Screwdriver	P1, P2, SL 1/4", SL 3/16", SQ1, SQ2, SQ3, ECX1, ECX2, T10, T15, T20, T25 and 1/4" Nut Driver
48-22-2901	27-in-1 Multi-Bit Screwdriver	P0, P1, P2, P3, SL 1/4", SL 3/16", SL 7/32", SL 9/32", SQ1, SQ2, SQ3, ECX1, ECX2, T10, T15, T20, T25, T30, 2MM, 2.5MM, 3MM, 4MM, 1/8" hex, 5/32" hex, 3/16" hex, 1/4" hex, and 1/4" Nut Driver
48-22-2904	27-in-1 Ratcheting Multi-Bit Screwdriver	P0, P1, P2, P3, SL 1/4", SL 3/16", SL 7/32", SL 9/32", SQ1, SQ2, SQ3, ECX1, ECX2, T10, T15, T20, T25, T30, 2MM, 2.5MM, 3MM, 4MM, 1/8" hex, 5/32" hex, 3/16" hex, 1/4" hex, and 1/4" Nut Driver
48-22-2907	14-in-1 TORX Multi-Bit Screwdriver	P1, P2, SL 1/4", SL 3/16", SQ1, SQ2, SQ3, ECX1, ECX2, T10, T15, T20, T25 and 1/4" Nut Driver
48-22-2908	14-in-1 Hex Multi-Bit Screwdriver	2MM, 2.5MM, 3MM, 4MM, 5MM, 6MM, 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", and 1/4" Nut Driver
48-22-2910	8-in-1 Compact Multi-Bit Screwdriver	P1, P2, SL 3/16", SL 1/4", SQ1, SQ2, T15, and 1/4" Nut Driver
48-22-2913	8-in-1 Ratcheting Compact Multi-Bit Screwdriver	P1, P2, SL 3/16", SL 1/4", SQ1, SQ2, T15, and 1/4" Nut Driver
48-22-2905	2pc 14-in-1 Ratcheting Multi-Bit and 8-in-1 Ratcheting Compact Multi-bit Screwdriver Set	Regular Handle: P1, P2, SL 1/4", SL 3/16", SQ1, SQ2, SQ3, ECX1, ECX2, T10, T15, T20, T25 and 1/4" Nut Driver Compact Handle: P1, P2, SL 3/16", SL 1/4", SQ1, SQ2, T15, and 1/4" Nut Driver
48-22-2930	4-in-1 Precision Multi-Bit Screwdriver	P00, P0, SL 1/8", SL 3/32"

INSULATED SCREWDRIVER

- FLAME & IMPACT RESISTANT
- DUAL LAYER INSULATION
- VISIBLE ID MARK



PART #	DESCRIPTION
48-22-2211	#1 Phillips - 76mm (3") 1000V Insulated Screwdriver
48-22-2212	#2 Phillips - 101mm (4") 1000V Insulated Screwdriver
48-22-2213	#3 Phillips - 152mm (6") 1000V Insulated Screwdriver
48-22-2221	1/4" Slotted - 152mm (6") 1000V Insulated Screwdriver
48-22-2222	5/16" Slotted - 177mm (7") 1000V Insulated Screwdriver
48-22-2223	3/8" Slotted - 203mm (8") 1000V Insulated Screwdriver
48-22-2224	3/8" Slotted - 254mm (10") 1000V Insulated Screwdriver
48-22-2231	3/16" Cabinet - 101mm (4") 1000V Insulated Screwdriver
48-22-2232	3/16" Cabinet - 152mm (6") 1000V Insulated Screwdriver
48-22-2233	3/16" Cabinet - 203mm (8") 1000V Insulated Screwdriver
48-22-2210	10pc 1000V Insulated Screwdriver Set w/ EVA Foam Case
48-22-2204	4pc 1000V Insulated Screwdriver Set w/ Roll Pouch

CUSHION GRIP SCREWDRIVER

- PRECISE FIT – REDUCES STRIPPING
- ANTI-SLIP TIP – LASER ETCHED
- LONG LASTING – HIGH STRENGTH BORON-INFUSED STEEL
- COMFORTABLE, CUSHION GRIP HANDLE
- VISIBLE ID MARKINGS



NEW

PART #	DESCRIPTION	BIT TYPES
MT200-4	4PC Cushion Grip Screwdriver Set (USA)	#2 Phillips x 4", 1/4" SL x 4", 3/16" Cabinet x 6", 5/16" SL x 6"
MT200-6	6PC Cushion Grip Screwdriver Set (USA)	5/16" SL x 6", 1/4" SL x 4", 3/16" Cabinet x 6", #1 Phillips x 3", #2 Phillips x 4", #3 Phillips x 6
MT201	#1 Phillips 3" Cushion Grip Screwdriver (USA)	
MT202	#2 Phillips 4" Cushion Grip Screwdriver (USA)	
MT203	#3 Phillips 6" Cushion Grip Screwdriver (USA)	
MT204	#2 Phillips 10" Cushion Grip Screwdriver (USA)	
MT205	#2 Phillips 6" Cushion Grip Demolition Screwdriver (USA)	
MT206	1/4" Slotted 4" Cushion Grip Screwdriver (USA)	
MT207	5/16" Slotted 6" Cushion Grip Screwdriver (USA)	
MT208	5/16" Slotted 6" Cushion Grip Demolition Screwdriver (USA)	
MT209	3/8" Slotted 8" Cushion Grip Screwdriver (USA)	
MT210	3/8" Slotted 8" Cushion Grip Demolition Screwdriver (USA)	
MT211	3/16" Cabinet 3" Cushion Grip Screwdriver (USA)	
MT212	3/16" Cabinet 6" Cushion Grip Screwdriver (USA)	
MT213	3/16" Cabinet 8" Cushion Grip Screwdriver (USA)	
MT214	1/4" Cabinet 10" Cushion Grip Screwdriver (USA)	
MT215	#1 ECX 4" Cushion Grip Screwdriver (USA)	
MT216	#2 ECX 4" Cushion Grip Screwdriver (USA)	
MT217	#1 Square 3" Cushion Grip Screwdriver (USA)	
MT218	#2 Square 4" Cushion Grip Screwdriver (USA)	
MT219	#3 Square 6" Cushion Grip Screwdriver (USA)	

