



# PL-S Short 2-Pin Base

## PL-S 13W/850/2P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

General Information	
Cap-Base	GX23
Life to 50% Failures (Nom)	10,000 hour(s)

Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux	810 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	13 W
Lamp Current (Nom)	0.290 A

Controls and Dimming	
Dimmable	No


Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

Product Data	
Order product name	PL-S 13W/850/2P 1CT/5X10BOX ALTO
Full product name	PL-S 13W/850/2P 1CT/5X10BOX ALTO
Order code	146878
Material Nr. (12NC)	927902785021
Numerator - Quantity Per Pack	1
Net Weight (Piece)	35.000 g
EAN/UPC - Product/Case	046677146870
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677146875



# PL-S Short 2-Pin Base

## Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-S 13W/850/2P 1CT/5X10BOX	28 mm	13 mm	139.5 mm	155.2 mm	177.7 mm
ALTO					

## Lifetime



Life expectancy diagram - 12 hour cycle

Life expectancy diagram - 3 hour cycle



Lumen Maintenance Diagram - PL-S 13W/850/2P 1CT/5X10BOX ALTO

## PL-S Short 2-Pin Base

