



Rapid Start T12

F96T12/DX/HO/ALTO 15PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	R17d (RDC)
Features	ALTO® (ALTO)
Light Technical	
Color Code	57
Luminous Flux	6,750 lm
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	90
Operating and Electrical	
Power Consumption	110 W
Mechanical and Housing	
Bulb Shape	T-12


Approval and Application	
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	F96T12/DX/HO/ALTO 15PK
Full product name	F96T12/DX/HO/ALTO 15PK
Order code	214890
Material Nr. (12NC)	927894705701
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.442 kg
EAN/UPC - Product/Case	046677214890
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677214895

Rapid Start T12

Dimensional drawing

Product

F96T12/DX/HO/ALTO 15PK



T12 Recessed Double Contact

