



# Switch Start Metal Halide Standard

## MH175/C/U 12PK

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

### Product data

| General Information              |                                  |
|----------------------------------|----------------------------------|
| Cap-Base                         | E39 [Single Contact Mogul Screw] |
| Warm-up time to 60% light <120 s |                                  |
| Controls and Dimming             |                                  |
| Dimmable                         | No                               |
| Mechanical and Housing           |                                  |
| Bulb Finish                      | Coated glass                     |
| Bulb Material                    | Hard Glass                       |
| Bulb Shape                       | BD17                             |
| Approval and Application         |                                  |
| Mercury (Hg) Content (Max)       | 30 mg                            |
| Product Data                     |                                  |
| Order product name               | MH175/C/U 12PK                   |

## Switch Start Metal Halide Standard

|                               |                |
|-------------------------------|----------------|
| Full product name             | MH175/C/U 12PK |
| Order code                    | 287284         |
| Material Nr. (12NC)           | 928601150403   |
| Numerator - Quantity Per Pack | 1              |
| Net Weight (Piece)            | 0.001 kg       |

|                                 |                |
|---------------------------------|----------------|
| EAN/UPC - Product/Case          | 046677287283   |
| Numerator - Packs per outer box | 12             |
| EAN/UPC - Case                  | 50046677287288 |

### Dimensional drawing

| Product        | D (max) | C (max) |
|----------------|---------|---------|
| MH175/C/U 12PK | 90 mm   | 206 mm  |

