



T5 High Output

F39T5/835/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Product data


General Information				
Cap-Base	G5			
Features	HO Alto® [High Output Alto]			
Light Technical				
Color Code	835 [CCT of 3500K]			
Luminous Flux	3,500 lm			
Luminous Efficacy (rated) (Nom)	82 lm/W			
Color Designation	White (WH)			
Correlated Color Temperature (Nom)	3500 K			
Color rendering index (CRI)	82			
Operating and Electrical				
Power Consumption	38.0 W			
Lamp Current (Nom)	0.325 A			
Controls and Dimming				
Dimmable	Yes			

Mechanical and Housing				
Bulb Shape	T5			
Approval and Application				
Mercury (Hg) Content (Nom)	1.4 mg			
Product Data				
Order product name	39W/835 Min Bipin T5 HO ALTO UNP			
Full product name	F39T5/835/HO/ALTO 40PK			
Order code	290239			
Material Nr. (12NC)	927992683522			
Numerator - Quantity Per Pack	1			
Net Weight (Piece)	78.000 g			
EAN/UPC - Product/Case	046677290238			
Numerator - Packs per outer box	40			
EAN/UPC - Case	50046677290233			

Datasheet, 2023, April 14 data subject to change


T5 High Output

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
39W/835 Min Bipin T5 HO ALTO	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm
UNP					


Photometric data



Spectral Power Distribution Colour - 39W/835 Min Bipin T5 HO ALTO UNP

Lifetime





Life expectancy diagram - 3 hour cycle

Lumen Maintenance Diagram - 39W/835 Min Bipin T5 HO ALTO UNP

T5 High Output

Lifetime

Life expectancy diagram - 12 hour cycle

