



Ceramalux ALTO

C1000S52/ALTO

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.


Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Luminous Efficacy (rated) (Nom)	135 lm/W
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	121.5 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	1,003 W
Lamp Current (Nom)	4.7 A
Voltage (Nom)	250 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	E25
Approval and Application	
Mercury (Hg) Content (Nom)	32 mg
Product Data	
Order product name	C1000S52/ALTO
Full product name	C1000S52/ALTO
Order code	368837
Material Nr. (12NC)	928601139205
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.001 kg
EAN/UPC - Product/Case	046677368838
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677368833

Ceramalux ALTO

Dimensional drawing



Product

C1000S52/ALTO

