



U-Bent Rapid Start T8

FB32T8/TL835/6 ALTO 20PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

Light Technical	
Color Code	TL835 [CCT of 3500K (835)]
Luminous Flux	2,800 lm
Color Designation	TL835
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	85

Operating and Electrical	
Power Consumption	32 W

Mechanical and Housing	
Bulb Shape	T8-6U [U-bent T 8/8 inch with 6" spacing]

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg

Product Data	
Order product name	FB32T8/TL835/6 ALTO 20PK
Full product name	FB32T8/TL835/6 ALTO 20PK
Order code	379008
Material Nr. (12NC)	927860083502
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.001 kg
EAN/UPC - Product/Case	046677379001
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677379006

U-Bent Rapid Start T8

Dimensional drawing

Product

FB32T8/TL835/6 ALTO 20PK

