



High Output T12

F96T12/CW/HO-O ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

| General Information | |
|------------------------------------|-----------------|
| Cap-Base | R17d (RDC) |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Color Code | 33 |
| Luminous Flux | 8,800 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4100 K |
| Color rendering index (CRI) | 62 |
| Operating and Electrical | |
| Power Consumption | 110 W |
| Mechanical and Housing | |
| Bulb Shape | T-12 |


| Approval and Application | |
|---------------------------------|---|
| Energy Saving Product | Not Applicable |
| Mercury (Hg) Content (Nom) | 6.8 mg |
| Product Data | |
| Order product name | TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP |
| Full product name | F96T12/CW/HO-O ALTO 15PK |
| Order code | 381764 |
| Material Nr. (12NC) | 927895203323 |
| Numerator - Quantity Per Pack | 1 |
| Net Weight (Piece) | 0.442 kg |
| EAN/UPC - Product/Case | 046677381769 |
| Numerator - Packs per outer box | 15 |
| EAN/UPC - Case | 50046677381764 |

High Output T12

Dimensional drawing

Product

TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP



T12 Recessed Double Contact

