



# High CRI T12

## FB40/T12/CW Supreme/6 12PK

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Light Technical	
Luminous Flux	2,300 lm
Color Designation	Cool White Supreme
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	90
Operating and Electrical	
Power Consumption	40 W
Mechanical and Housing	
Bulb Shape	T12-6U [U-bent T 12/8 inch with 6" spacing]
Approval and Application	
Energy Saving Product	Not Applicable

Mercury (Hg) Content (Nom)	10.0 mg
Product Data	
Order product name	FB40/T12/CW Supreme/6 12PK
Full product name	FB40/T12/CW Supreme/6 12PK
Order code	423087
Material Nr. (12NC)	927862003702
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.001 kg
EAN/UPC - Product/Case	046677423087
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677423082

## High CRI T12

### Dimensional drawing

#### Product

FB40/T12/CW Supreme/6 12PK

