



TuffGuard Coated T12

F96T12/CW Supreme/ALTO TG

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.

Product data

General Information	
Cap-Base	FA8 [FA8]
Features	ALTO® (ALTO)

Light Technical	
Luminous Flux	5,000 lm
Color Designation	Cool White Supreme
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	89

Operating and Electrical	
Power Consumption	75 W

Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	6.8 mg

Product Data	
Order product name	F96T12/CW Supreme/ALTO TG 15PK
Full product name	F96T12/CW Supreme/ALTO TG
Order code	423160
Material Nr. (12NC)	927895003705
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677423162
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677423167

TuffGuard Coated T12

Dimensional drawing

Product

F96T12/CW Supreme/ALTO TG 15PK

