



# High CRI T12

## F40T12/C50Supreme/ALTO 30pk

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

  

Light Technical	
Luminous Flux	2,545 lm
Color Designation	C50 Supreme
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	90

  

Operating and Electrical	
Power Consumption	40 W

  

Mechanical and Housing	
Bulb Shape	T-12

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg

  

Product Data	
Order product name	F40T12/C50Supreme/ALTO 30pk
Full product name	F40T12/C50Supreme/ALTO 30pk
Order code	423897
Material Nr. (12NC)	927888000213
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.230 kg
EAN/UPC - Product/Case	046677423896
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677423891

# High CRI T12

## Dimensional drawing

### Product

F40T12/C50Supreme/ALTO 30pk

