



PL-T Triple 4-Pin Base

PL-T 32W/835/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

General Information	
Cap-Base	GX24q-3

Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	2,250 lm
Color Designation	White (WH)
Luminous Efficacy (rated) (Nom)	68.2 lm/W
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	33.0 W
Lamp Current (Nom)	0.320 A


Controls and Dimming	
Dimmable	Yes

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

Product Data	
Order product name	PL-T 32W/835/A/4P 1CT/5X10BOX ALTO
Full product name	PL-T 32W/835/A/4P 1CT/5X10BOX ALTO
Order code	458307
Material Nr. (12NC)	927911083550
Numerator - Quantity Per Pack	1
Net Weight (Piece)	70.000 g
EAN/UPC - Product/Case	046677268336
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677458305


PL-T Triple 4-Pin Base

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
PL-T 32W/835/A/4P 1CT/5X10BOX ALTO	41 mm	98.7 mm	123.0 mm	138.7 mm

Photometric data




Spectral Power Distribution Colour - PL-T 32W/835/A/4P 1CT/5X10BOX ALTO

Lifetime




Lumen Maintenance Diagram - PL-T 32W/835/A/4P 1CT/5X10BOX ALTO



Life expectancy diagram - 3 hour cycle

PL-T Triple 4-Pin Base

Lifetime



Life expectancy diagram - 12 hour cycle

