



Ceramalux ALTO

C70S62/ALTO 12PK

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Luminous Efficacy (rated) (Nom)	94 lm/W
Chromaticity Coordinate X (Nom)	522
Chromaticity Coordinate Y (Nom)	425
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	86 lm/W
Color rendering index (CRI)	13
Operating and Electrical	
Power Consumption	70.2 W
Lamp Current (Nom)	1.6 A
Voltage (Nom)	52 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2

Approval and Application

Mercury (Hg) Content (Max)	17 mg
----------------------------	-------

Product Data

Order product name	SON 70W E39 ED75 CL SL/12
Full product name	C70S62/ALTO 12PK
Order code	467258
Material Nr. (12NC)	928601139990
Numerator - Quantity Per Pack	1
Net Weight (Piece)	108.000 g
EAN/UPC - Product/Case	046677467258
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467253

Ceramalux ALTO

Dimensional drawing

Product

SON 70W E39 ED75 CL SL/12

