



Ceramalux ALTO

C400S51/ALTO 12PK

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Luminous Efficacy (rated) (Nom)	125 lm/W
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	112.5 lm/W
Color rendering index (CRI)	20
Operating and Electrical	
Power Consumption	401.5 W
Lamp Current (Nom)	4.6 A
Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED18
Approval and Application	
Mercury (Hg) Content (Max)	23.5 mg
Product Data	
Order product name	SON 400W E39 ED58 CL SL/12
Full product name	C400S51/ALTO 12PK
Order code	467373
Material Nr. (12NC)	928601139391
Numerator - Quantity Per Pack	1
Net Weight (Piece)	165.000 g
EAN/UPC - Product/Case	046677467371
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467376

Ceramalux ALTO

Dimensional drawing

Product

SON 400W E39 ED58 CL SL/12

