



Corepro InstantFit (UL Type-A) T8

10T8/COR/48-830/IF15/G/DIM 10/1

The CorePro InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only CorePro InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality CorePro InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the CorePro InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

Product data


General Information		Color rendering index (CRI)		82
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	LLMF At End Of Nominal Lifetime (Nom)		70 %
Nominal lifetime	70,000 hour(s)	Operating and Electrical		
Switching Cycle	50,000	Line Frequency	25000-105000 Hz	
Lighting Technology	LED	Input Frequency	25000-105000 Hz	
Light Technical		Power Consumption	10 W	
Color Code	830 [CCT of 3000K]	Lamp Current (Max)	260 mA	
Beam Angle (Nom)	240 degree(s)	Lamp Current (Min)	100 mA	
Luminous Flux	1,500 lm	Wattage Equivalent	32 W	
Color Designation	White (WH)	Starting Time (Nom)	0.5 s	
Luminous Efficacy (rated) (Nom)	160.00 lm/W	Warm-up time to 60% light	0.5 s	
Correlated Color Temperature (Nom)	3000 K	Power Factor (Fraction)	0.9	
Color Consistency	<6	Voltage (Nom)	120-277, 347 V	

Corepro InstantFit (UL Type-A) T8

UL Type	UL Type A
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance



Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	10T8/COR/48-830/IF15/G/DIM 10/1
Full product name	10T8/COR/48-830/IF15/G/DIM 10/1
Order code	553214
Material Nr. (12NC)	929002252734
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.230 kg
EAN/UPC - Product/Case	046677553210
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677553215

Dimensional drawing



Product	D1	D2	A1	A2	A3
10T8/COR/48-830/IF15/G/DIM 10/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm

Photometric data




Accent Lighting Spots - 10T8/COR/48-830/IF15/G/DIM 10/1

Light Distribution Diagram - 10T8/COR/48-830/IF15/G/DIM 10/1



Corepro InstantFit (UL Type-A) T8

Photometric data





Spectral Power Distribution Colour - 10T8/COR/48-830/IF15/G/DIM 10/1

Lifetime



LEDtube 70K 5070 FailureRate-LED

Life Expectancy Diagram




LEDtube 70K 5070 LifetimeVsTc-LED

Lumen Maintenance Diagram - 10T8/COR/48-830/IF15/G/DIM 10/1

Corepro InstantFit (UL Type-A) T8

Lifetime



Lumen Maintenance Diagram - 10T8/COR/48-830/IF15/G/DIM 10/1

