



PANDUIT PART NUMBER #	MATERIAL SUFFIX	MATERIAL	WEIGHT lbs/100 pcs (g)/100 pcs
ABM100-S6	NONE	NYLON 6/6 (WHITE)	0.26/ 100 pcs (119)/ 100 pcs
	-0	WEATHER RESISTANT NYLON (BLACK)	
	-69	FLAME RETARDANT NYLON (IVORY)	




NOTES:

*1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

2. HOLE FOR STANDARD S6 FLAT HEAD SCREW.

3. USE MOUNTS WITH THESE CABLE TIES CROSS SECTION:
M, I, S
SG200, SG250, SG300

							TITLE ABM100-S6 4 WAY MOUNT CUSTOMER DRAWING							
06A	4/8/2024	RVU	MSAD	DJSL	A. REPLACED OLD PANDUIT LOGO TO "P" ON MODEL.	GAECN07078	ITEM REVISION NAME G03597HJ/02				PANDUIT			
5	8/3/16	RVU	CLW	JHAC	CHANGE FROM .25 [6.4] TO .20 +/- .02.	GAECN03564	DATASET FILE NAME G03597HJ_DC/02C GB0239DB_06A CUST DWG							
4	3/3/05	JAD			UPDATE CABLE TIE WINDOW DIMENSIONS FOR NEW SUPER GRIP TIES, ADD NOTE 3.	GB0239DB	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .05 [1.3] .xxx ± .010 [0.25] .xx ± .02 [0.5] ANGLES ± 5 °  THIRD ANGLE PROJECTION				MATERIAL: SEE TABLE			
3	5/9/01	LGG			REMOVED -14 AND -15 MATERIAL, BOTH ARE OBS.	GB0239DB					FMEA & CONTROL PLAN NUMBER: G03597HJ			
2	12/19/99	CGSM			CHANGED DIMENSION TOLERANCES. REMOVED HOLD DIMENSIONS, ADD NOTE 2.	GB0239DB					INSPECTION INSTRUCTION NUMBER: GI0033BA			
1	12/16/96	AJV			MODIFIED PART GEOMETRY AND ADDED MATERIAL TABLE.	GB0239DB					DRAWING NUMBER: GB0239DB			
R	5/14/96	CJG			INITIAL RELEASE.	GB0239DB					SHEET 1 OF 1			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY CJG	DATE 5/14/96	CHK MSAD	SCALE 2X	DRAWING NUMBER: GB0239DB		SIZE 1 OF 1	A

PANDUIT

MATERIAL:

SEE TABLE

FMEA & CONTROL PLAN NUMBER:

G03597HJ

INSPECTION INSTRUCTION NUMBER:

GI0033BA