



FF-90-2M - 90° 3/4" Iron Elbow, Female/Female

By Killark
Catalog # [FF-90-2M](#)

90° 3/4" Iron Elbow, Female/Female.



*Representative Image

Features

- Threaded for rigid conduit or IMC
- Smooth integral bushings to prevent damage to wires
- Fileté pour conduit rigide ou IMC
- bagues intégrales lisses pour éviter d'endommager les fils.

General

Application	
Catalog Number	FF-90-2M
Color	
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Material	Iron
Series	FF
Type	
UPC	783936170244

Dimensions

Dimensions	3 in x 2 in x 3 in
Gross Weight with Packaging	0.45
Height	3 in
Hub Size	3/4"
Length	3 in
Width	2 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
UL File Number	E10514

Logistics

Carton Quantity 10

Product Assets

[Catalogs - Killark Catalog](#)
[Certifications - FF, MF, & MM Series Elbows UL Certification](#)
[Certifications - Elbows CSA Certification \(BL, FF, MF, MM Series\)](#)
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-FF902M-SPEC-EN | REV 6/2024