



# FXS Series 3-Pole Tumbler Switch Cover With Device - Factory Sealed - 15A

By Killark  
Catalog # FXS-8C

FXS Series - Aluminum 3-Pole Tumbler Switch Cover With Device - Factory Sealed - 15A.



\*Representative Image

### Features

- Eliminates external sealing requirements.
- Lower installation cost.
- NEMA 3 weatherproof.
- Color coded wiring with more wiring space for easier field installation.
- Stainless steel captive screws for cover assembly.
- Lockout accessory available must be factory installed.
- Ground boss for grounding in the splicebox.
- Device bodies and covers are copper-free cast aluminum alloy.
- Push button, selector switches and pilot light bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

### General

Action	3P
Actuator	Lever
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Application	
Back Box Type	FXB
Catalog Number	FXS-8C
Color	Gray
	Gris
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	3
Series	FXS
Type	
UPC	783936194899

### Dimensions

Depth	3.15
Dimensions	6.5 in x 6.125 in x 4.75 in
Gross Weight with Packaging	3.2
Height	4.75 in
Length	6.5 in
Width	6.125 in

### Electrical Ratings

Amperage Rating	15 A
Frequency Rating	50/60 Hz

### Certifications And Compliance

CSA File Number	LR11712
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class I, Zones 1 & 2, Groups IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
Nema Rating	3
UL File Number	E53360, E10501

### Logistics

Carton Quantity	5
-----------------	---

### Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - FXS & XS Series UL Certification](#)
- [Certifications - FXB, FXCS, & FXS Series Control Stations UL Certification](#)
- [Certifications - FXS, XS, XST Series CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)

