



GECXT-2 - 3/4" GEC Outlet Body X Type

By Killark
Catalog # GECXT-2

3/4" GEC Outlet Body X Type.



*Representative Image

Features

- Internally threaded cover openings for additional wiring room
- Covers furnished with boxes
- Weather-resistant finish
- Green ground screw standard.

General

Application	
Catalog Number	GECXT-2
Color	
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Hub Pattern	X
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GE
Type	
UPC	783936210155

Dimensions

Dimensions	6.25 in x 6 in x 4.25 in
Gross Weight with Packaging	1.84
Height	4.25 in
Hub Size	3/4"
Length	6.25 in
Weight	1.84 lb
Width	6 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class I, Zones 1 & 2, Groups IIB, IIA
UL File Number	E10514

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - GE Series Outlet Bodies UL Certification](#)
- [Certifications - GEC Series Luminaire Fittings UL Certification](#)
- [Certifications - GE Series Outlet Boxes ATEX Certificate](#)
- [Certifications - GEC Series CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_GEC Series Outlet Bodies IOM_K1457](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-GECXT2-SPEC-EN | REV 6/2024