



GESXT-4 - 1-1/4" GES Outlet Body X Type, Aluminum

By Killark
Catalog # [GESXT-4](#)

1-1/4" GES Outlet Body X Type, Aluminum.



*Representative Image

Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

General

Application	
Catalog Number	GESXT-4
Color	Gray
	Gris
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Hub Pattern	X
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GE
Type	
UPC	783936210360

Dimensions

Dimensions	8.125 in x 6 in x 7 in
Gross Weight with Packaging	3.17
Height	7 in
Hub Size	1-1/4"
Length	8.125 in
Width	6 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Group D
	Class I, Zones 1 & 2, Group IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

- [3D Models - GESXT-4 3D Model](#)
- [Certifications - GES Series Outlet Bodies UL Certification](#)
- [Certifications - GE Series Outlet Boxes ATEX Certificate](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - GESXT-4 Engineering Drawing](#)
- [Installation Manuals - KIL_GE Series Outlet Bodies IOM_K1431](#)
- [Sales Drawings - GESXT-4 Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-GESXT4-SPEC-EN | REV 6/2024