



GUML-1 - 1/2" 90° Angle Union, Male to Female

By Killark
Catalog # [GUML-1](#)

1/2" 90° Angle Union Male to Female.



*Representative Image

Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction
- Fileté pour conduit rigide ou IMC
- Filetage conique (NPT)
- Construction solide et durable

General

Application	
Catalog Number	GUML-1
Color	
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GUM
Type	
UPC	783936270210

Dimensions

Dimensions	3 in x 2 in x 3 in
Gross Weight with Packaging	0.16
Height	3 in
Hub Size	1/2"
Length	3 in
Weight	0.16 lb
Width	2 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A, B, C, D Class I, Zones 1 & 2, Groups IIC, IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
UL File Number	E10514

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Certifications - GUML Series Unions UL Certification](#)
[Certifications - GUF/GUM Series Unions CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-GUML1-SPEC-EN | REV 6/2024