



## OLB-2M - 3/4" LB Hub, Iron O Series Conduit Body

By Killark  
Catalog # [OLB-2M](#)



3/4" LB Hub, Iron O Series Conduit Body.

\*Representative Image

### Features

- Raintight when used with gasketed covers.
- Malleable iron suitable for use in concrete.
- Interchangeable with competitive products.
- Stainless steel screws on stamped and cast covers.
- Tapered threaded hubs (NPT).

### General

Application	
Catalog Number	OLB-2M
Color	Gray
	Gris
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Hub Pattern	LB
Material	Iron
Series	O Series
Type	
UPC	783936480435

### Dimensions

Dimensions	6 in x 2 in x 3 in
Gross Weight with Packaging	1.05
Height	3 in
Hub Size	3/4"
Length	6 in
Weight	1.05 lb
Width	2 in

### Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

### Logistics

Carton Quantity 5

### Product Assets

[Catalogs - Killark Catalog](#)  
[Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)  
[Customer Notices - Prop 65 Notice](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-OLB2M-SPEC-EN | REV 6/2024