



OX-6 - 2" X Hub, Aluminum O Series Conduit Body

By Killark
Catalog # [OX-6](#)



*Representative Image

Features

- Raintight when used with gasketed covers.
- Malleable iron suitable for use in concrete.
- Interchangeable with competitive products.
- Stainless steel screws on stamped and cast covers.
- Tapered threaded hubs (NPT).

General

Application	
Catalog Number	OX-6
Color	Gray
	Gris
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Hub Pattern	X
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
Type	
UPC	783936550060

Dimensions

Dimensions	12 in x 6 in x 4 in
Gross Weight with Packaging	2.5
Height	4 in
Hub Size	2"
Length	12 in
Width	6 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [3D Models - OX-6 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - OX-6 Engineering Drawing](#)
- [Sales Drawings - OX-6 Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-OX6-SPEC-EN | REV 6/2024