



R-51 - 1½" to ½" Reducing Bushing

By Killark
Catalog # R-51

1½" to ½" Reducing Bushing.



*Representative Image

Features

- Tapered threads (NPT)
- Smooth internal bushing protects conductors
- Threaded for Rigid Conduit or IMC
- Filetages coniques (NPT)
- la bague interne lisse protège les conducteurs
- fileté pour conduit rigide ou IMC

General

Application	
Catalog Number	R-51
Color	
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	R
Type	
UPC	783936570075

Dimensions

Dimensions	1 in x 2 in x 2 in
Gross Weight with Packaging	0.19
Height	2 in
Hub Size	1-1/2" to 1/2"
Length	1 in
Weight	0.19 lb
Width	2 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A, B, C, D Class I, Zones 1 & 2, Groups IIC, IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G
UL File Number	E10514

Logistics

Carton Quantity 20

Product Assets

[Certifications - Adapter & Reducer Series Conduit Fittings UL Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - R & RE Series Reducers IOM K1413](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-R51-SPEC-EN | REV 6/2024