



# XCS Series Control Station Cover - Maintained Contact 2-Position Selector Switch Cover With Device - "Off - On" Nameplate - 1NO/1NC Contact Rating

By Killark  
Catalog # XCS-OS2A1

XCS Series - Aluminum Maintained Contact 2-Position Selector Switch Cover With Device - "Off - On" Nameplate - 1NO/1NC Contact Rating.



\*Representative Image

## General

Action	Rotary
Actuator	2 Position Selector Switch
Application	
Back Box Type	SWB
Catalog Number	XCS-OS2A1
Color	
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	1
Series	XCS
Type	
UPC	783936890135

## Dimensions

Depth	3-5/16
Dimensions	6.875 in x 5.75 in x 4.75 in
Gross Weight with Packaging	1.52
Height	4.75 in
Length	6.875 in
Width	5.75 in

## Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 6A BREAKING @ 120 VAC; 3A BREAKING @ 240 VAC; 1.5A BREAKING @ 480 VAC; 1.2A BREAKING @ 600 VAC; 10A CARRYING @ 120 VAC; 10A CARRYING @ 240 VAC; 10A CARRYING @ 480 VAC;
Frequency Rating	50/60 Hz

## Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D Class I, Zones 1 & 2, Groups IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
UL File Number	E53360

## Product Assets

- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SWB Series Control Stations IOM K0569F](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-XCSOS2A1-SPEC-EN | REV 6/2024