



# XCS-OB4-U - XCS Series, AL Momentary Contact Double Push Button Cvr w/ Device, Green Button w/ Start Nameplate, Red Button w/ Stop Nameplate, 2NO/2NC

By Killark  
Catalog # XCS-OB4-U

XCS Series - Aluminum Momentary Contact Double Push Button Cover With Device - Green Button With "Start" Nameplate - Red Button With "Stop" Nameplate - 2NO/2NC Contact Rating.



\*Representative Image

## General

Action	SP (per circuit)
Actuator	Momentary Pushbutton
Application	
Back Box Type	SWB
Catalog Number	XCS-OB4-U
Color	
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	2
Series	XCS
Type	
UPC	783936890241

## Dimensions

Depth	1-3/4
Dimensions	6.375 in x 5.875 in x 4.375 in
Gross Weight with Packaging	1.46
Height	4.375 in
Length	6.375 in
Width	5.875 in

## Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 6A BREAKING @ 120 VAC; 3A BREAKING @ 240 VAC; 1.5A BREAKING @ 480 VAC; 1.2A BREAKING @ 600 VAC; 10A CARRYING @ 120 VAC; 10A CARRYING @ 240 VAC; 10A CARRYING @ 480 VAC;
Frequency Rating	50/60 Hz

## Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D Class I, Zones 1 & 2, Groups IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
UL File Number	E53360

## Product Assets

- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SWB Series Control Stations IOM K0569F](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-XCS0B4U-SPEC-EN | REV 6/2024