



## Y-1 - 90° 1/2", Capped Elbow

By Killark  
Catalog # Y-1

90° 1/2", Capped Elbow.



\*Representative Image

### Features

- Threaded for rigid conduit or IMC
- Smooth integral bushings to prevent damage to wires
- Fileté pour conduit rigide ou IMC
- bagues intégrales lisses pour éviter d'endommager les fils.

### General

Application	
Catalog Number	Y-1
Color	
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	Y
Type	
UPC	783936970011

### Dimensions

Dimensions	3 in x 2 in x 3 in
Gross Weight with Packaging	0.27
Height	3 in
Hub Size	1/2"
Length	3 in
Weight	0.27 lb
Width	2 in

### Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
UL File Number	E10514

### Logistics

Carton Quantity 10

### Product Assets

[3D Models - Y-1 3D Model](#)  
[Certifications - BL & Y Series Elbows UL Certification](#)  
[Certifications - Y Series CSA Certification](#)  
[Customer Notices - Prop 65 Notice](#)  
[Engineering Drawing - Y-1 Engineering Drawing](#)  
[Sales Drawings - Y-1 Sales Drawing](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-Y1-SPEC-EN | REV 6/2024