



Y-2M - 90° 3/4" Iron, Capped Elbow

By Killark
Catalog # Y-2M

90° 3/4" Iron, Capped Elbow.



*Representative Image

Features

- Threaded for rigid conduit or IMC
- Smooth integral bushings to prevent damage to wires
- Fileté pour conduit rigide ou IMC
- bagues intégrales lisses pour éviter d'endommager les fils.

General

Application	
Catalog Number	Y-2M
Color	
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Material	Iron
Series	Y
Type	
UPC	783936970110

Dimensions

Dimensions	4 in x 3 in x 4 in
Gross Weight with Packaging	1.04
Height	4 in
Hub Size	3/4"
Length	4 in
Weight	1.04 lb
Width	3 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
UL File Number	E10514

Logistics

Carton Quantity 5

Product Assets

[Certifications - BL & Y Series Elbows UL Certification](#)
[Certifications - Y Series CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-Y2M-SPEC-EN | REV 6/2024