



## Y-3M - 90° 1" Iron, Capped Elbow

By Killark  
Catalog # Y-3M

90° 1" Iron, Capped Elbow.



\*Representative Image

### Features

- Threaded for rigid conduit or IMC
- Smooth integral bushings to prevent damage to wires

### General

Application	
Catalog Number	Y-3M
Color	Gray
	Gris
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Material	Iron
Series	Y
Type	
UPC	783936970127

### Dimensions

Dimensions	4 in x 3 in x 4 in
Gross Weight with Packaging	1.77
Height	4 in
Hub Size	1"
Length	4 in
Weight	1.77 lb
Width	3 in

### Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E10514

### Logistics

Carton Quantity 2

### Product Assets

[Certifications - BL & Y Series Elbows UL Certification](#)  
[Certifications - Y Series CSA Certification](#)  
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-Y3M-SPEC-EN | REV 6/2024