



UGP Series - 15 Amp 125VAC Interchangeable Blade Style Plug With Quick Wiring - NEMA Configuration 5-15P

By Killark
Catalog # [UGP-15231QW](#)



*Representative Image

UGP Series - Aluminum 15 Amp 125VAC Interchangeable Blade Style Plug With Quick Wiring - NEMA Configuration 5-15P.

General

Application	
Catalog Number	UGP-15231QW
Color	
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	2
Receptacle Type	Delayed Action
Series	UGP
Type	
UPC	783936076683

Dimensions

Dimensions	6.625 in x 2.375 in x 1.875 in
Gross Weight with Packaging	0.4
Height	1.875 in
Length	6.625 in
Width	2.375 in

Electrical Ratings

Amperage Rating	15 A
-----------------	------

Conductor Related

Number Of Wires	3
Wire Size	#10 AWG, #12 AWG, or #14 AWG

Certifications And Compliance

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class I, Zones 1 & 2, Groups IIB, IIA
	Class II, Divisions 1 & 2, Groups F, G
	Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X

Logistics

Carton Quantity	54
-----------------	----

Product Assets

- [3D Media - KIL_UGP-15231QW](#)
- [Certifications - UGR/UGP Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - UGP-15231QW Engineering Drawing](#)
- [Installation Manuals - UGP Series IOM K1377](#)
- [Sales Drawings - UGP-15231QW Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-UGP15231QW-SPEC-EN | REV 6/2024