

Eaton TRUSBDAC20W-BOX

Catalog Number: TRUSBDAC20W-BOX

Eaton Combination USB Type-AC Charger with Power Delivery, 20A 5-20R Receptacle, 60W, 125Vac, W



General specifications

Product Name	Catalog Number
Eaton USB with power delivery	TRUSBDAC20W-BOX
UPC	Product Length/Depth
032664016226	1.79 in
Product Height	Product Width
4.21 in	2.03 in
Product Weight	Certifications
0.39 lb	cULus Listed

Type

Type AC

Amperage Rating

20A

Voltage rating

125V

Features

Tamper resistant

60 W charging

Wiring method

Back and side wire

Color

White

Wattage

60W

Allowable wire size

#14-12 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-in

Brochures

USB PD application guide

USB PD sell sheet

Multimedia

Fast and convenient charging made easy with Eaton's USB receptacles

Eaton's USB charging receptacles - Never miss a moment

Introduction to USB-C Duplex Receptacles

Specifications and datasheets

USB PD type ac 60W spec sheet