

Eaton 1301BK

Catalog Number: 1301BK

Eaton toggle switch, #14-10 AWG, 15A, Flush, 120V, Side and push, Screw, Black, Single-Pole, Single-Pole, Polycarbonate



General specifications

Product Name	Catalog Number
Eaton toggle switch	1301BK
UPC	Product Length/Depth
032664745386	1.31 in
Product Height	Product Width
3.28 in	0.88 in
Product Weight	Compliances
0.16 lb	NAFTA
	RoHS Compliant
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Type

Toggle switch

Amperage Rating

15A

Voltage rating

120 V

Number Of Poles

Single-pole

Application

Residential

Wiring method

Side and push

Switch type

Single-pole

Mounting method

Flush

Connector type

Screw

Material

Polycarbonate

Allowable wire size

#14-10 AWG

Torque rating

14 lbf-inch

Color

Black

Resources

Specifications and datasheets

[Eaton Specification Sheet - 1301BK](#)

[Residential grade toggle switches spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)