

Eaton TR7765B-BOX

Catalog Number: TR7765B-BOX

Eaton combination 3.6A USB charger with duplex receptacle, 15A, 125V, BR - TR7765B-BOX



General specifications

Product Name	Catalog Number
Eaton combination USB charger with duplex receptacle	TR7765B-BOX
	UPC
	032664766978
Product Length/Depth	Product Height
1.4 in	4.19 in
Product Width	Product Weight
1.3 in	0.793 lb
Certifications	
cULus Listed	

defaultTaxonomyAttributeLabel

Type

Type A

Amperage Rating

15A

Voltage rating

125 V

Contact material

Brass

Features

Tamper resistant

3.6A Charging

Wiring method

Screw terminals

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Packaging type

Retail Box

Color

Brown

Material

Thermoplastic

Style

Decorator

Allowable wire size

#12-14 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Combination type

USB

Resources

Brochures

[USB Duplex Receptacle Devices Brochure](#)

Multimedia

[Eaton's USB charging receptacles - Never miss a moment](#)

[Fast and convenient charging made easy with Eaton's USB receptacles](#)

[Introduction to USB-C Duplex Receptacles](#)

Specifications and datasheets

[Combination USB 3.6A charger with TR duplex receptacle](#)

[Eaton Specification Sheet - TR7765B-BOX](#)

Design type

Receptacle

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)