

# Eaton TR1877LABXSP

Catalog Number: TR1877LABXSP

Eaton commercial specification grade single receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Side wire, Light almond, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, Single, Screw, PVC, ED Box



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton commercial specification grade single receptacle	TR1877LABXSP
	<b>UPC</b>
	032664750212
<b>Product Length/Depth</b>	<b>Product Height</b>
1.3 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
0.87 in	0.155 lb
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	cULus Listed NOM

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Single receptacle

### Amperage Rating

20A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

Tamper resistant

### Application

Commercial

### Device grade

Commercial

### Wiring method

Side wire

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

PVC

### Packaging type

ED Box

### Color

Light almond

### Connection type

Screw

## Resources

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TR1877LABXSP](#)

[Commercial grade straight blade duplex receptacles spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

PVC body

Impact-resistant thermoplastic face

Receptacle type

Single



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)