

Eaton TR1877V-BXSP

Catalog Number: TR1877V-BXSP

Eaton commercial specification grade single receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Side wire, Ivory, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, Single, Screw, PVC, ED Box



General specifications

Product Name	Catalog Number
Eaton commercial specification grade single receptacle	TR1877V-BXSP
	UPC
	032664750229
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.87 in	0.155 lb
Compliances	Certifications
RoHS Compliant	cULus Listed NOM

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Single receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Auto-grounding

Tamper resistant

Application

Commercial

Device grade

Commercial

Wiring method

Side wire

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

PVC

Packaging type

ED Box

Color

Ivory

Connection type

Screw

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR1877V-BXSP](#)

[Commercial grade straight blade duplex receptacles spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face

PVC body

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia